

## DSUB FE 3W3 SHELL W/O CONTACTS



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 200 0033
Specification	DSUB FE 3W3 SHELL W/O CONTACTS
HARTING eCatalogue	<a href="https://b2b.harting.com/09692000033">https://b2b.harting.com/09692000033</a>

### Identification

Category	Connectors
Series	D-Sub
Identification	Mixed
Element	Connector
Description of the contact	Straight

### Version

Gender	Female
Size	D-Sub 2
Number of contacts	3
Number of signal contacts	0
Number of special contacts	3
Locking type	Fixing flange with feed through hole $\varnothing$ 3.1 mm
Details	Please order special contacts separately.

### Technical characteristics

Insulation resistance	$> 5 \times 10^9 \Omega$
Limiting temperature	-55 ... +125 °C
Mating cycles	$\geq 500$
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
Hot plugging	No



Pushing Performance

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (Polyester) Shell: steel, tin plated
Colour (insert)	Green
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead Antimony trioxide

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
----------	-----------------------

## Commercial data

Packaging size	100
Net weight	7.06 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440214 D-Sub coupler

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09692000033](#)