

**Model:TR28-H7.4-150**

Working temperature	: -20°C ~ +60°C
Sensitivity	95±3dB SPL @1KHz (0dB SPL=20μPa)Input voltage: 60mV (Sine wave) measured with.
Ac impedance degrees	150±20% Ω(@ 1KHz 60mV)
Rated power	10mW
Max. Power	30mW

Drainig

