

## Coaxial Cable Connector 11\_N-50-7-44/133\_N

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
Frequency range	DC to 2 GHz
Return loss	30 dB

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0291 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Brass	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00006130
Catalogue drawing	DOU-00006132
Assembly instruction	DOC-0000179092

### Ordering Information

Single package	11_N-50-7-44/133_NE
Bulk 100 pcs package	11_N-50-7-44/133_NH

### Additional Information

Suitable cables	RG_214_U, GX_07272_D, GX_07272_D-04, RADOX_RF_214
-----------------	---