

Coaxial Cable Connector 24_N-50-3-51/19-_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
Frequency range	DC to 12 GHz
Return loss	30 dB

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0484 kg

Environmental Data

Operating temperature	-55 °C to 70 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel / Brass	
Insulator	Air Dielectric - Bead - PPH	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Brass	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DCA-00009706
Assembly instruction	DOC-0000180866

Ordering Information

Single package	24_N-50-3-51/19-_NE
----------------	---------------------

Additional Information

Suitable cables	EZ_141_TP_M17, MULTIFLEX_141, SUCOFORM_141_CU
-----------------	---