

SHUNTS & JUMPERS



(2.54 mm) .100" PITCH • SNT/MNT/2SN/SNM/PK/JL SERIES

SNT/MNT

Mates:
TSW, HTSW, MTSW,
HMTSW, TLW, DW, EW,
ZW, HW, TSM, BST, PHT

2SN

Mates:
TMMH, TMM,
MTMM, MMT, TW,
LTMM, ZLTMM, TSH, EHT

SNM

Mates:
TMS, MTMS, DWM

SPECIFICATIONS

SNT

Insulator Material:
Glass Filled Polyester
Contact Material:
Phosphor Bronze
Current Rating (SNT/TSW):
4.3 A per pin
(1 pin powered per row)
Operating Temp Range:
-55 °C to +125 °C
Insertion Depth:
(4.32 mm) .170" minimum
Lead Size accepted:
(0.64 mm) .025" SQ

MNT


Same as SNT except:
Current Rating (MNT/TSM):
3.9 A per pin
(1 pin powered per row)
Working Voltage:
450 VAC

2SN


Same as SNT except:
Insertion Depth:
(2.29 mm) .090" minimum
Lead Size accepted:
(0.51 mm) .020" SQ

SNM


Same as SNT except:
Insertion Depth:
(3.43 mm) .135" minimum
Max Processing Temp:
Not recommended for IR/VPT




Note:
Other Gold plating options available.



Note:
Some lengths, styles and options are non-standard, non-returnable.




JL



PART NO.	A
JL-100-25-T	(2.54) .100
JL-250-25-T	(6.35) .250
JL-400-25-T	(10.16) .400

Note:
For complete specifications see www.samtec.com?JL

PK



PART NO.	A	B
PK-01-06	(0.64) .025 SQ	(5.84) .230
PK-01-07	(0.51) .020 SQ	(3.18) .125

Insulator Material:
Natural Thermoplastic

Note:
Order per wheel.
6 pins per wheel.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[MNT-105-BK-G](#) [MNT-102-BK-T](#) [MNT-102-BK-G](#) [MNT-103-BK-T](#) [MNT-104-BK-G](#) [MNT-110-BK-G](#) [MNT-103-BK-G](#)
[MNT-108-BK-T](#) [MNT-114-BK-G](#) [MNT-120-BK-G](#) [MNT-104-BK-T](#) [MNT-105-BK-T](#) [MNT-108-BK-G](#) [MNT-112-BK-G](#)
[MNT-106-BK-G](#) [MNT-109-BK-G](#) [MNT-107-BK-G](#) [MNT-103-BK-H](#) [MNT-113-BK-G](#) [MNT-107-BK-H](#) [MNT-118-BK-H](#)
[MNT-109-BK-H](#) [MNT-115-BK-H](#) [MNT-115-BK-T](#) [MNT-116-BK-H](#) [MNT-116-BK-T](#) [MNT-106-BK-H](#) [MNT-106-BK-T](#)
[MNT-112-BK-H](#) [MNT-112-BK-T](#) [MNT-113-BK-H](#) [MNT-111-BK-H](#) [MNT-115-BK-G](#) [MNT-117-BK-H](#) [MNT-118-BK-G](#)
[MNT-120-BK-T](#) [MNT-114-BK-H](#) [MNT-110-BK-T](#) [MNT-113-BK-T](#) [MNT-105-BK-H](#) [MNT-107-BK-T](#) [MNT-108-BK-H](#)
[MNT-102-BK-H](#) [MNT-109-BK-T](#) [MNT-110-BK-H](#) [MNT-116-BK-G](#) [MNT-117-BK-G](#) [MNT-117-BK-T](#) [MNT-120-BK-H](#)
[MNT-104-BK-H](#) [MNT-111-BK-G](#) [MNT-111-BK-T](#) [MNT-114-BK-T](#) [MNT-118-BK-T](#) [MNT-119-BK-G](#) [MNT-119-BK-T](#)
[MNT-101-BK-G](#)