


(1,27 mm) .050"
PCMT, PCMS SERIES

PCMCIA TERMINAL & SOCKET STRIPS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?PCMT

Insulator Material: Black Liquid Crystal Polymer
Terminal Material: Phosphor Bronze
Plating: Sn or Au over 50µ" (1,27 µm) Ni
Current Rating: 2A per contact @ 80°C ambient
Operating Temp Range: -55°C to +105°C with Tin; -55°C to +125°C with Gold
Lead-Free Solderable: Yes
SMT Lead Coplanarity: (0,15 mm) .006" max
RoHS Compliant: Yes



Note: Some lengths, styles and options are non-standard, non-returnable.

PCMT - 134 - LEAD STYLE - PLATING OPTION - D - RA - CARD LENGTH - SL

Mates with: PCMS

Specify LEAD STYLE from chart

-L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail
-S = 30µ" (0,76 µm) Gold on post, Matte Tin on tail

-01 = (25,40 mm) 1.00" Card Length
-02 = (50,80 mm) 2.00" Card Length
-03 = (76,20 mm) 3.00" Card Length

CARD LENGTH	D	LEAD STYLE	Y	POSITION NUMBER	C (POST)
-01	(25,40) 1.00	-01	(6,35) .250	01, 17, 34, 35, 51, 68	(5,00) .197
-02	(50,80) 2.00	-01	(6,35) .250	36, 67	(3,50) .138
-03	(76,20) 3.00	-02	(8,89) .350	ALL OTHERS	(4,25) .167

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?PCMS

Insulator Material: Black Liquid Crystal Polymer
Contact Material: BeCu
Plating: Au or Sn over 50µ" (1,27 µm) Ni
Current Rating: 1A per contact
Operating Temp Range: -55°C to +125°C
Contact Resistance: 10 mΩ
Insertion Depth: (3,05 mm) .120" min
Insertion Force: (Single contact only) 4.0 oz (1,11 N) avg.
Withdrawal Force: (Single contact only) 3.0 oz (0,83 N) avg.
Lead-Free Solderable: Yes
SMT Lead Coplanarity: (0,10 mm) .004" max
RoHS Compliant: Yes



PCMS - 134 - CARD THICKNESS - PLATING OPTION - D

Mates with: PCMT

Note: Some sizes, styles and options are non-standard, non-returnable.

-01 = (0,80 mm) .031" thick board
-02 = (1,60 mm) .062" thick board

-L = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail
-S = 30µ" (0,76 µm) Gold on contact, Matte Tin on tail

CARD THICKNESS	A	B	C
-01	(1,02) .040	(1,79) .070	(3,12) .123
-02	(1,70) .067	(2,46) .097	(2,77) .109

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[PCMT-134-02-L-D-RA-02-SL](#)