


SPECIFICATION

1. Rated Voltage4.2Vrms(12Vp-p) Sine Wave
2. Max. Rated Input Voltage60Vp-p Square Wave
3. Min. Sound Pressure Level104±3dB at 4.2Vrms(12Vp-p)
Sine Wave/1-5KHz/30cm
4. Rated Frequency Range1-5KHz
5. Max. Capacitance at 100Hz170±30% nF
6. Shell Material/ColorPA66/Black
7. Cone Material.....PVC
8. Operating Temperature-40~+60°C
9. Store Temperature-40~+60°C
10. Weight9g
11. Terminal Pull-Out Force.....Min 7Lbs
12. Wire Pull-Out Force.....Min 1Lb
13. Disc To Cone Pull-Out Force.....Min 2.2Lbs
14. Glue Bubble Quantity/size.....Max 2/Ø2.5



				KEPO NINGBO KEPO ELECTRONIC CO.,LTD http://www.chinaacoustic.com	
				Ultra Sonic Transducer System Sensor	
				PCT-4540PAM	
No.	DESCRIPTION	APPROVED	DATE		
TOLERANCES UNLESS NOTED OTHERWISE		APPROVALS		DATE	
X : A		DRAWN		UNIT	DWG NO.
XX : A		CHECKED		mm	OEM1447
XXX : A		APPROVED		SCALE	SHEET
90 : ± FORWARD ±2 ;				08.06.18	NOT TO SCALE
ANGLES : ±1 ;					VER 1.9