

FEATURES

- High-impact-resistant thermoplastic
- Moulded threads
- Resistant to most chemicals, oils and grease
- Matte Black
- Temperature rating - 20 to + 110°C
- No chipping or cracking

RS PRO Black Ball Clamping Knob, M10

RS Stock No.: 702-7784



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Knobs are used in a wide variety of applications in our day-to-day lives and perform many functions, from being used as fixed handles to being used to tighten, loosen, adjust, clamp and push other components or pieces of equipment. They are used in various applications, from industrial and construction machinery to audio and visual equipment.

Female knobs: M4 (RS [7027796](#)), M5 (RS [7027790](#)), M6 (RS [7027787](#)), M8 (RS [7027800](#)), M8 (RS [7027780](#)), M10 (RS [7027784](#)), M12 (RS [7027793](#)).

General Specifications


Thread	M10
Knob Shape	Ball
Mounting Type	Threaded Hole
Body Material	High impact resistant thermoplastic
Colour	Black
Finish	matt finish
Application	Levers & handles, Furniture, Appliances, Tools, Machine jigs

Mechanical Specifications

Thread Diameter	10mm
Knob Diameter	45mm
Hole Diameter	18mm
Hole Length	43mm

Approvals

Compliance/Certifications	EN61340
----------------------------------	---------



Part No.	A	B	C	Thread size
7027796	15	14	10	M4
7027790	20	19	10	M5
7027787	25	23	13	M6
7027800	32	30	14	M8
7027780	38	36	18	M8
7027784	45	43	18	M10
7027793	50	49	19	M12