








Econoseal J Series Connectors <Mark II (+)>

Contact

Contact	Wire Range	Wire Ins. Diameter	Material/Finish	Part No.		Hand Tool No. (Instruction Sheet)
				S.T.	L.P.	
.070 Water proof Tab 	0.2-0.5mm ² (AWG#24-20)	Ø1.4-2.4mm	Brass/Pre-tin	171631-1	173600-1	91563-1 (411-5254)
			Brass/Sel. Gold	171631-2	—	
	0.5-1.25mm ² (AWG#20-16)	Ø2.0-2.6mm	Brass/Pre-tin	171661-1	173706-1	91585-1 (411-5322)
			Brass/Sel. Gold	171661-2	—	
Crimp Specifications : 114-5082						
.070 Water proof Receptacle 	0.2-0.5mm ² (AWG#24-20)	Ø1.4-2.4mm	Brass/Pre-tin	171630-1	171699-1	91563-1 (411-5254)
			Copper Alloy/Sel. Gold	171630-5	—	
	0.5-1.25mm ² (AWG#20-16)	Ø2.0-2.6mm	Brass/Pre-tin	171662-1	173707-1	91583-1 (411-5322)
			Copper Alloy/Pre-tin	171662-4	—	
			Copper Alloy/Sel. Gold	171662-5	—	
Crimp Specifications : 114-5082						

Rubber Plug and Cavity Plug

Description	Style	Wire Ins. Diameter	Material/Color	Part No.
Rubber Plug (S Size)		Ø1.4-2.4mm	NBR/Black	172746-1
		Ø1.4-2.1mm	NBR/Black	178210-1
Rubber Plug (M Size)		Ø2.0-2.6mm	NBR/Gray	172888-2
			Silicon/Brown	1-172888-3
		Ø1.8-2.6mm	NBR/Gray	176886-2
Cavity Plug		—	NBR/Black	172748-1
			NBR/Gray	172748-2