


**Specification:**

| Model | DC.CAB.8410.0150 |
|-----------------------|----------------------|
| DC Socket | 5.5/2.5 mm |
| Recommended voltage | 0 - 48V |
| Max Current | 5 A |
| Dielectric Strength | 500 VDC |
| Operating temperature | -25°C to +70°C |
| Cord Length | 1500 mm |
| Cable Diameter | 2,00 x 4,10 mm |
| Wire Diameter | 2x0,5mm ² |
| ROHS | + |

**Made in Poland**