

Product Name	Current transformer	Model	SCT013-060
--------------	---------------------	-------	------------

Characteristics: Opening size 13mm\*13mm, 1m leading wire, standard  $\Phi 3.5$  three-core plug output.  
voltage output type.

Purpose: Used for current measurement, monitor and protection for AC motor, lighting equipment, air compressor etc.  
Patent No.: ZL 2015 3 0060067. X


### Technical Data

$I_{PN}$	Rated input	0-60A
$I_{PM}$	Max. detection input	
$I_{OUT}$	Rated output	0-1V
X	Accuracy	$\pm 1\%$
$\epsilon_L$	Linearity	$\leq 0.2\%$
N	Turns ratio	1:1800
$\Phi$	Phase shift	
$R_L$	Max. Sampling resistance	
$V_{PN}$	Work voltage	660V
f	Work frequency	50-1KHz
$T_A$	Operating temperature	-25..+70°C
$T_S$	Storage temperature	-40..+85°C
Vd	Dielectric strength, 50 Hz, 1 min	3KV



Fire resistance	UL94-V0
Material of core	Ferrite
Mounting type	Suspension
Weight	55g

Dimension ( mm(in). 1 mm= 0.0394 inch)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Seeed Studio:](#)

[101990065](#) [101990058](#) [101990061](#) [101990062](#) [101990063](#) [101990064](#)