

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 11\_QMA-50-3-2/133\_N

Rev.: C



### Description

Straight cable plug for flexible cable

Interface standards  
QMA QLF compliant



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
Frequency range	DC to 1 GHz
Return loss	≥ 32 dB

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0051 kg

#### Environmental Data

Operating Temperature	-40 °C to 85 °C
2002/95/EC (RoHS)	compliant

#### Material Data

##### Piece Parts

Centre contact	Brass
Outer contact	Bronze
Body	Brass
Insulator	PFA / PTFE
Crimp ferrule	Copper

##### Surface Plating

SUCOPRO Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

#### Related Documents

Outline drawing	DOU-00007410
Catalogue drawing	DOU-00006724

#### Ordering Information

Single package	11_QMA-50-3-2/133_NE
Bulk 100 pcs package	11_QMA-50-3-2/133_NH

#### Additional Information

Suitable cables	RG_58_C/U, G_03232, GX_03272
-----------------	------------------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**