


Product family: Brass cable glands - Metric thread
Item code: 2512L, 2517L, 2520L, 2525L, 2532L, 2540L, 2550L, 2563L
Description: BRASS CABLE GLANDS · METRIC THREAD · IP68 · WITH LONG THREAD

Image




Technical drawing



Specifications

MATERIAL: nickel-plated brass
OPERATING TEMPERATURE: from -40 °C to +100 °C
INNER GASKET AND O-RING: NBR (nitrile rubber), 70 Shore A
ACCORDING TO STD.: EN 62444:2013
ASSEMBLY: do not remove or move the gasket; tighten on a flat and smooth surface.
CAGE IN: polyamide (PA 6.6)

Code	Metric thread size (EN60423)	Ø cable (mm)	L (mm)	E wrench (nut)	E1 wrench (locknut)	
2512L	M 12 x 1.5	3 - 6,5	10	14	14	25/25
2517L	M 16 x 1.5	4 - 8	10	18	18	25/25
2520L	M 20 x 1.5	6 - 12	10	22	22	25/25
2525L	M 25 x 1.5	10 - 14	12	27	24	25/25
2532L	M 32 x 1.5	15 - 22	14	34	34	10/10
2540L	M 40 x 1.5	18 - 25	15	45	45	5/5
2550L	M 50 x 1.5	32 - 38	15	58	58	5/5
2563L	M 63 x 1.5	37 - 44	15	68	64	5/5

