



General ordering data

Order No.	9019240000
Part designation	H10,0/22D R
Version	Wire end ferrule, 10 mm ² , 12 mm, Colour code: DIN, red
EAN	4008190075385
Qty	100 pc(s).

Technical data

Length	22 mm
Width	8.4 mm
Height	8.4 mm

Product data

Conductor nominal cross-section	10 mm ²
AWG	7
Total length (L1)	22 mm
Contact surface length (L2)	12 mm
Contact surface diameter (D1)	4.5 mm
Collar diameter (D2)	7.6 mm
Metal sleeve thickness (S1)	0.2 mm
Plastic collar thickness (S2)	0.4 mm

Approvals

Approval body



Classifications

ETIM 2.0	EC000005
ETIM 3.0	EC000005
eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01
eClass 5.1	27-40-02-01

Classifications

Similar products

Order No.	Part designation	Version
056580000	H10,0/28 EB	Wire end ferrule, 10 mm ² , 18 mm, Colour code: Weidmüller, ivory
901925000	H10,0/28D R	Wire end ferrule, 10 mm ² , 18 mm, Colour code: DIN, red
902116000	H10,0/28T BR	Wire end ferrule, 10 mm ² , 18 mm, Colour code: Miscellaneous, brown
053420000	H10,0/22 EB	Wire end ferrule, 10 mm ² , 12 mm, Colour code: Weidmüller, ivory
901924000	H10,0/22D R	Wire end ferrule, 10 mm ² , 12 mm, Colour code: DIN, red
902115000	H10,0/22T BR	Wire end ferrule, 10 mm ² , 12 mm, Colour code: Miscellaneous, brown