MALLORY Mallory Sonalert Products Inc.	Part #	PT-1240PQ
Sales Outline Drawing	Revision	E

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

	to discuss jour approunding
Resonant Frequency (Hz)	4100 ± 500
Operating Voltage (Vp-p/max)	20
Rated Voltage (Vp-p)	5.0
Current Consumption (mA/max)	2.0 at Rated Voltage
Sound Pressure Level (dB/min)	80 at 10cm at Rated voltage
Capacitance (pF)	$17,000 \pm 30\%$ at 120 Hz
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin
	(Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	0.8
Condition by wave soldering (°C)	$245 \pm 5 / 3 \pm 0.5 \text{ sec}$
Condition by hand soldering (°C)	350 ± 20 / within 5 sec
Options	For other options contact factory

NO CIRCUITRY

Dimensions: (units: mm)

ROHS Compliant

