


KPS-1500 SERIES PIEZO SIREN

DIMENSIONS

Model No	KPS-1500
Rated Voltage	12 VDC
Operating Voltage	6~15 VDC
Max. Rated Current	≤300mA
Min. S.P. L	105dB at 12VDC /100cm
Resonant Frequency	1.5 ~ 4KHz
Tone Nature	Siren
Operating Temperature	-20 ~ +60 °C
Store Temperature	-30 ~ +70 °C
Weight	110 g



Color Black
ABS Housing Material
Steel Tab Mounted




all dimensions are in mm

* Value applying at rated voltage


KPS-6000 SERIES PIEZO SIREN

DIMENSIONS

Model No	KPS-6000	KPS-6000-24
Rated Voltage	12 VDC	24VDC
Operating Voltage	6~15 VDC	12~27VDC
Max. Rated Current	280mA/12 VDC	160mA / 24VDC
Min. S.P. L	105dB at 12VDC/100cm	104dB at 24VDC /100cm
Resonant Frequency	2.8±0.5KHz	2.8±0.5KHz
Tone Nature	Siren	Single
Operating Temperature	-20 ~ +60 °C	-20 ~ +60 °C
Store Temperature	-30 ~ +70 °C	-30 ~ +70 °C
Weight	70g	80g



Color White
ABS Housing Material
Piezo Screamer Water proof



all dimensions are in mm

* Value applying at rated voltage


KPS-6210 SERIES PIEZO SIREN

DIMENSIONS

Model No	KPS-6210	KPS-6210-24
Rated Voltage	12 VDC	24VDC
Operating Voltage	6~15 VDC	6~30VDC
Max. Rated Current	280mA/12 VDC	150mA / 24VDC
Min. S.P. L	105±2dB at 12VDC/100cm	105±2dB at 24VDC /100cm
Resonant Frequency	1.5~3.5KHz	1.5~3.5KHz
Tone Nature	Siren	Siren
Operating Temperature	-20~+60 °C	-20~+60 °C
Store Temperature	-30~+70 °C	-30~+70 °C
Weight	129g	130g



Color Black
ABS Housing Material





all dimensions are in mm

* Value applying at rated voltage

KPS-8555 SERIES PIEZO SIREN

DIMENSIONS





Color White
ABS Housing Material
Piezo Screamer

Model No	KPS-8555
Rated Voltage	12 VDC
Operating Voltage	6~15 VDC
Max. Rated Current	100mA
Min. S.P. L	105dB at 12VDC /100cm
Tone Nature	Siren
Operating Temperature	-20 ~ +60 °C
Store Temperature	-30 ~ +70 °C
Weight	85 g

* Value applying at rated voltage

KPS-8555A SERIES PIEZO SIREN

DIMENSIONS




color Black
ABS Housing Material
Lead Terminal

Model No	KPS-8555A
Rated Voltage	12VDC
Operating Voltage	6 ~ 15VDC
Max. Rated Current	100mA
Min. S.P. L	106dB at 12VDC/100cm
Tone Nature	Siren
Housing Material/Color	ABS/White
Operating Temperature	-20 ~ +70 °C
Store Temperature	-20 ~ +80 °C
Weight	85g

* Value applying at rated voltage

KPS-91G-PZ SERIES PIEZO SIREN

DIMENSIONS



color Black
ABS Housing Material
Lead Terminal

Model No	KPS-91G-PZ
Rated Voltage	12VDC
Operating Voltage	8 ~ 15VDC
Max. Rated Current	650mA
Min. S.P. L	112dB at 12VDC/100cm
Tone Nature	Siren
Shell Material/Color	ABS/Black
Operating Temperature	-20 ~ +60 °C
Store Temperature	-30 ~ +70 °C
Weight	200g

* Value applying at rated voltage