


1 2 3 4 5 6 7 8

A

A

B

B



# SPECIFICATION


- 1. Rated Voltage .....14VDC
- 2. Operating Voltage .....6~16VDC
- 3. Max. Rated Current .....250mA/14VDC
- 4. Min. Sound Pressure Level.....98dB/100cm/14VDC
- 5. Tone Nature .....6Tone
- 6. Case Material .....ABS
- 7. Operating Temperature .....-20~+60°C
- 8. Store Temperature .....-30~+70°C
- 9. Weight .....80g

C

C

D

D



E

E

F

F

				<b>KEPO</b> NINGBO KEPO ELECTRONIC CO.,LTD <a href="http://www.chinaacoustic.com">http://www.chinaacoustic.com</a>	
				<b>Electronic siren</b>	
				<b>KPS-1520-6T</b>	
No.	DESCRIPTION	APPROVED	DATE		
TOLERANCES UNLESS NOTED OTHERWISE X * .XX * .XXX * 90° FORMED +2 * ANGLES -1 *		APPROVALS	DATE	UNIT	DWG NO.
FIRST ANGLE PROJECTION		DRAWN		mm	KP3.842.494
		CHECKED		SCALE	SHEET
		APPROVED	07.04.06	NOT TO SCALE	VER 1.1

1 2 3 4 5 6 7 8