

Han 3A-HTE plastic (9-17mm)



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 0410
Specification	Han 3A-HTE plastic (9-17mm)
HARTING eCatalogue	https://b2b.harting.com/19200030410

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Hood
Description of hood/housing	With integrated cable gland

Version

Size	3 A
Version	Top entry
Cable entry	1x Integrated
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12
Cable diameter	9 ... 17 mm

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)



Pushing Performance

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

Commercial data

Packaging size	10
Net weight	17.31 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19200030410](#)