Mallory Sonalert Produc	ts Inc. Part # PT-2726PQ
Sales Outline Drawing	Revision D
May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.	
Operating Voltage (Vp-p/max)	30
Rated Voltage (Vp-p)	5.0
Current Consumption (mA/max)	1.5 at Rated Voltage
Sound Pressure Level (dB/min)	90 at 10cm at Rated voltage
Capacitance (pF)	$30,000 \pm 30\%$ at 120 Hz
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin
-	(Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	4.4
Condition by wave soldering (°C)	245 ±5 / 3±0.5 sec
Condition by hand soldering (°C)	350 ± 20 / within 5 sec
Options	For other options contact factory
NO CIRCUITRY Dimensions: (units: mm)	ROHS Compliant

