
Item no.: 2002-1407
Product description: 4-Conductor earth terminal block suitable for Ex e applications



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm ²]	0.25 - 4 mm ²
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Nominal current (Ex e II)	22 A
Weight	9.333 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	33 mm
Height	1.299 in
Width	5.2 mm
Width	0.205 in
Depth	70 mm

Depth	2.76 in
Strip length from	10 mm
Strip length to	12 mm



Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
2002-1407	ABS	05-HG476175/3-PDA			0,5-4
2002-1407	AEX	E185892			22-12
2002-1407	CCA	NL6387			0,2-2,5/4
2002-1407	CSA	154112-1536069			22-12
2002-1407	DNV	E-10423			0,5-4
2002-1407	GL	26187-05HH			0,25-2,5
2002-1407	KEMA	NL2116586.02			0,5-4
2002-1407	LR	91/20112(E6)			0,5-4
2002-1407	PRS	TE/1718/880590/08			0,2-4
2002-1407	PTB	IECEXPTB03.0004U			0,2-4
2002-1407	PTB	PTB03AteX1162U			0,2-4
2002-1407	RosTest	8189158			0,2-4
2002-1407	UR	E45172			22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected