


Deep groove ball bearings, single row, shield on both sides

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
25	52	15	14,8	7,8	0,335	28000	14000	0,13	6205-2Z *



Calculation factors

k_r 0,025

f_0 14