


# Metric Spacers

SPACERS

## Threaded Female Spacers

- Available in a variety of standard body lengths.
- Brass spacers: base material is free-machining brass, with nickel plating.
- Plastic material: Nylon 66 UL94V-2.
- Longer thread lengths may not be threaded through the complete length, but have female threads at both ends.



HEXAGONAL	CIRCULAR
<p><b>Materials</b></p> <p>Base material: Brass or Plastic</p> <p>Finish: Nickel</p> <p>Brass: Nickel</p>	<p><b>Materials</b></p> <p>Base material: Brass</p> <p>Finish: Nickel</p> <p>Brass: Nickel</p>
<p>5.00 A/F (R25-100, R30-100) 5.50 A/F (R30-101, R30-161) 7.00 A/F (R40-100)</p> <p>M2.5 (R25), M3 (R30) or M4 (R40)</p> <p>Length</p>	<p>Ø4.76</p> <p>M3</p> <p>Length</p>

### HOW TO ORDER

**RXX - XXX XX XX**

SERIES CODE	
<b>R25-100</b>	Hexagonal, Brass, M2.5 Thread
<b>R30-100</b>	Hexagonal, Brass, M3 Thread
<b>R30-101</b>	Hexagonal, Brass, M3 Thread
<b>R30-161</b>	Hexagonal, Plastic, M3 Thread
<b>R30-500</b>	Circular, Brass, M3 Thread
<b>R40-100</b>	Hexagonal, Brass, M4 Thread

FINISH	
<b>00</b>	White (Plastic only)
<b>02</b>	Nickel (Brass only)

LENGTH (mm)	
<b>06 to 16, 18, 20, 25</b>	R30-161, R40-100
<b>04 to 16, 18, 20, 25</b>	Other

All dimensions in mm.