



Ethernet Switch Ha-VIS mCon 7100-B1V

10-port Ethernet Switch for industrial Ethernet networks,
with M12 system cabling

Managed	IP65 / IP67	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
Number of ports, Copper / Termination	10x 10/100Base-T(X) / M12 D-coding (female)		
Input voltage / Termination	24 / 48 V DC / M12 A-coding, male, for redundant power supply		
Permissible range (min./max.)	12 V ... 60 V DC		
Input current	approx. 180 mA (at 24 V DC)		
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A M12 D-coding, male		
Housing material	zinc die-cast		
Dimensions (W x H x D)	90 x 120 x 87 mm		
Weight	approx. 1.4 kg		
Working temperature	-40 °C ... +70 °C		
MTBF	378.000 h		
Management	fully managed via Web interface and SNMP Functions see pages 01.141 and 01.142		

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS mCon 7100-B1V Ethernet Switch with 10 ports M12 D-coding	20 70 310 4945		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[20703104945](#)