

Adapter M12 RJ45 Cat 5a straight



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 381 2401
Specification	Adapter M12 RJ45 Cat 5a straight
HARTING eCatalogue	https://b2b.harting.com/21033812401

Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	M12 female-RJ45 panel feed through
Description of the accessory	D-coding 4 poles Straight

Version

Gender	Female
--------	--------

Technical characteristics

Mating cycles	≥100
Thickness of the panel	2.1 ... 4.5 mm

Material properties

Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

Material properties

ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	47.4 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440292 Connector component (accessories)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21033812401](#)