


P1	COLOR
2	BLACK
3	RED
4	GREEN
5	YELLOW



Part Number	wire length	cut length
AT-S-26-6/4/X-5-OE	1525±20(5ft)	1525-1535mm
AT-S-26-6/4/X-7-OE	2135±30(7ft)	2135-2145mm
AT-S-26-6/4/X-10-OE	3050±60(10ft)	3050-3060mm
AT-S-26-6/4/X-12-OE	3660±60(12ft)	3660-3670mm
AT-S-26-6/4/X-14-OE	4270±60(14ft)	4270-4280mm
AT-S-26-6/4/X-25-OE	7625±100(25ft)	7625-7635mm
AT-S-26-6/4/X-50-OE	15250±150(50ft)	15250-15260mm

Note:

- Material: Housing-polycarbonate, clear Terminal-0.36[.014] thick phosphor bronze. Thick gold in localized gold plate. Area, Gold Flash over the remainder. Over 2.54mm[.100(.100)] thick nickel underplate.
- ① Operation temperature: -20° ~ +60°C Voltage rating: 150V Current rating: 1A max.

AT-S-26-6/4/X-XX-OE
 B:black, S:silver, W:white length in feet

ROHS compliant
 Unit: mm

Scale	Free	Customer-No.	
TOLERANCE		Drawn	28.06.2013
		Approved	06.04.2017
DIM	TOL	ASSMANN WSW-No. AT-S-26-6/4/X-XX-OE	
		Drawing-No. ASS 7953 CA	
Angle	TOL	Replace	
		Sheet	
①	①	Add operation temperature	
②	②	Drawn	
		Modification	
		Date	
		Name	



1	2	3	4	5	6	7
H	G	F	E	D	C	B