

Number of contacts

6, 10, 16, 24 +



Identification	Number of contacts	Part number		Drawing	Dimensions in mm
		Male insert	Female insert		
Left hand version Multi contour (MK)	6	09 33 006 4625	09 33 006 4725		
	10	09 33 010 4625	09 33 010 4725		
	16	09 33 016 4625	09 33 016 4725		
	24	09 33 024 4625	09 33 024 4725		
Left hand version Single contour (SK)	6	09 33 006 4626	09 33 006 4726		
	10	09 33 010 4626	09 33 010 4726		
	16	09 33 016 4626	09 33 016 4726		
	24	09 33 024 4626	09 33 024 4726		
Right hand version Multi contour (MK)	6	09 33 006 4635	09 33 006 4735		
	10	09 33 010 4635	09 33 010 4735		
	16	09 33 016 4635	09 33 016 4735		
	24	09 33 024 4635	09 33 024 4735		
Right hand version Single contour (SK)	6	09 33 006 4636	09 33 006 4736		
	10	09 33 010 4636	09 33 010 4736		
	16	09 33 016 4636	09 33 016 4736		
	24	09 33 024 4636	09 33 024 4736		

Han AV

	a	b
Han® 6 E AV	20	44
Han® 10 E AV	34	57
Han® 16 E AV	54	77.5
Han® 24 E AV	81	104

① Contact arrangement for male insert
 ② Contact arrangement for female insert

Stock items in bold type