

BoPad

Desktop enclosure, IP40 (IP65)



BOP 900 PH-9005

Order no.: 35190035

* = Available on request.

Characteristics

Colour of enclosure group

Black, similar to RAL 9005

Colour of enclosure group

Black

Protection class

IP 40, 65

Enclosure Material

Enclosures: ABS

Seal / impact protection: TPE

For details see technical information

Scope of delivery

Lid and base, 4 screws, 4 rubber feet

Note

Upgradable to IP65 with design seal BOP_DI.

Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.


» Additional information

Dimensions

Dimensions

200 x 105 x 53.6 mm

Product drawing



Technical drawings

3D product data in STEP format: Registration necessary

Drawing for mechanical processing: 35190035 BOP-900-PH-9005-G.dxf (1.5 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Product drawing in PDF format: 35190035 BOP-900-PH-9005.pdf (220.7 KB)

Product drawing in DXF format: 35190035 BOP-900-PH-9005.dxf (2.5 MB)

Drawing for max. PCB dimensions in PDF format: 35190035 BOP-900-PH-9005-pcb.pdf (181.3 KB)

Drawing for max. PCB dimensions in DXF format: 35190035 BOP-900-PH-9005-pcb.dxf (1.1 MB)

Matching accessories



Design seal, IP65

35290005	BOP 900 DI-9005	Black
35290006	BOP 900 DI-9016	White
35290000	BOP 900 DI-5005	Signal blue
35290001	BOP 900 DI-3001	Signal red



Screw covers for enclosure screws

35007405	BOP-SA-9005	Black
----------	-------------	-------



Universal VESA standard (75x75) wall fitting, polyamide glass fibre reinforced

35111005	VESA-WB-9005	Black
----------	--------------	-------



Screws (SHR) and distance bolts (DIBLZ) for mounting bosses in plastic enclosures

59006190	SHR Z KA25x6	SD = 2.5 / ND = 2.0 / KD = 4.4
----------	--------------	--------------------------------