



RT3MC-B

3 pole TINY xlr male cable connector, black metal shell, gold plated contacts, bulk packaging available (*-D)

- Easy to assemble
- Robust metal housing with best flex relief
- Shielded system – high noise immunity and EMI protection
- Intuitive and rugged locking mechanism provides secure locking system
- Millionfond proven chuck type strain relief – up to 4.00 mm cable diameter
- Keyed insert and strain relief to avoid mispositioning / rotation of insert respectively cable



Technical Information [hide](#)

| | |
|---------------------------|-------------------------------------|
| Product | |
| Title | RT3MC-B |
| Electrical | |
| Contact resistance | < 10 mΩ (inner) |
| Dielectric strength | > 0.5 kVdc |
| Insulation resistance | > 1 GΩ |
| Rated current per contact | < 5 A |
| Mechanical | |
| Cable O.D. | 2.0 - 4.0 mm |
| Lifetime | > 5000 mating cycles |
| Wiresize | 0.22 mm ² |
| Wiresize | 24 AWG |
| Material | |
| Boot | EPDM, ZnAl4Cu1, diecast rubber boot |
| Contacts | Bronze (CuSn6) |
| Shell | Zinc diecast (ZnAl4Cu1) |
| Strain relief | PVC |
| Environmental | |
| Temperature range | -30 °C to +85 °C |

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

REAN[®]
REAN a brand of Neutrik AG