ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	Α	Redrawn in Autocad	JAP	12/6/01				
1199	В	Redrawn and Renamed	JWM	11/9/01	JC	11/26/01	JC	11/26/01


## NOTES:

## MATERIAL:

1. ELECTRO-TIN PLATED COPPER WITH NYLON 6/6 FULL SLEEVE.

2. FLAMMABILITY: UL94V-2 3. VOLTAGE RATING: 600 V

4. OPERATING TEMP: -40°F(40°C) TO 167°F(75°C)







**OSHA** Acceptable

									<u>→</u>   Ø	M <del> </del>
PART NUMBER	WIRE RANGE (AWG)	MATES WITH MALE TAB WIDTH (W) X THICKNESS	L	E	В	Т	М	U	COLOR	Style
CFS-DY-1025	12 - 10	.250 x .032	.96	.32	.25	.165	.250	.020	YELLOW	1
CFS-DY-1412 †	16 - 14	.110 x .020	.80	.25	.19	.115	.145	.012	BLUE	3
CFS-DY-1418	16 – 14	.187 x .020	.77	.25	.25	.085	.170	.016	BLUE	1
CFS-DY-1425	16 – 14	.250 x .032	.86	.30	.25	.080	.170	.020	BLUE	2
CFS-DY-1818	22 – 18	.187 x .020	.77	.25	.25	.085	.145	.016	RED	1
CFS-DY-1825	22 – 18	.250 x .032	.86	.30	.25	.080	.145	.020	RED	2

 $\dagger$  not ul listed or CSA certified SPC-F004.DWG

DISCLAINER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

ATE AND RELIABLE. SINCE CONDITIONS DETERMINE THE SUITABILITY OF THE PF LIABILITY WHATSOEVER IN CONNECTION	RODUCT FOR THE	
DRAWN BY:	DATE:	DR

	DRAWN BY:	DATE:	
Tolerances: Unless Otherwise Specified:	JC	3/8/91	
$X = \pm .015$	CHECKED BY:	DATE:	
$.XX = \pm .010$ $.XXX = \pm .005$	JOHN COLE	12/10/91	
.AAA = ±.005	APPROVED BY:	DATE:	
	John Liska	12/10/91	



## **SPC TECHNOLOGY**

REV

RAWING TITLE: Nylon Insulated Female Disconnects SIZE ELECTRONIC FILE DWG. NO.

TA-445 TA-445.dwg В SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1