






Number of contacts

# 12+

10 A 400 V 6 kV 3

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																					
		Male	Female																						
Han® Q , With Han-Quick Lock® PE contact, Crimp termination  Blue slide Please order crimp contacts separately.	0,14 ... 2,5	09 12 012 3001	09 12 012 3101	 <p>M</p> <p>F</p> With Han-Quick Lock® PE contact : Conductor cross-section Blue slide 0.5 ... 2.5 Conductor cross-section Black slide 0.25 ... 1.5																					
Han® Q , With Han-Quick Lock® PE contact, Crimp termination  Black slide Please order crimp contacts separately.	0,14 ... 2,5	09 12 012 3004	09 12 012 3104																						
Han D® , Crimp contact, Contact surface: Silver plated 	0,14 ... 0,37 0,5 0,75 1 1,5 2,5	09 15 000 6104 09 15 000 6103 09 15 000 6105 09 15 000 6102 09 15 000 6101 09 15 000 6106	09 15 000 6204 09 15 000 6203 09 15 000 6205 09 15 000 6202 09 15 000 6201 09 15 000 6206	 <table border="1"> <thead> <tr> <th>Wire gauge</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm<sup>2</sup> AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm<sup>2</sup> AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm<sup>2</sup> AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm<sup>2</sup> AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup> AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup> AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Wire gauge	∅	Stripping length	0.14-0.37 mm <sup>2</sup> AWG 26-22	0.9 mm	8 mm	0.5 mm <sup>2</sup> AWG 20	1.1 mm	8 mm	0.75 mm <sup>2</sup> AWG 18	1.3 mm	8 mm	1 mm <sup>2</sup> AWG 18	1.45 mm	8 mm	1.5 mm <sup>2</sup> AWG 16	1.75 mm	8 mm	2.5 mm <sup>2</sup> AWG 14	2.25 mm	6 mm
Wire gauge	∅	Stripping length																							
0.14-0.37 mm <sup>2</sup> AWG 26-22	0.9 mm	8 mm																							
0.5 mm <sup>2</sup> AWG 20	1.1 mm	8 mm																							
0.75 mm <sup>2</sup> AWG 18	1.3 mm	8 mm																							
1 mm <sup>2</sup> AWG 18	1.45 mm	8 mm																							
1.5 mm <sup>2</sup> AWG 16	1.75 mm	8 mm																							
2.5 mm <sup>2</sup> AWG 14	2.25 mm	6 mm																							

Han Q