





REV.	CNN	CNN DESCRIPTION	Date	Check in
01		border change	11/04/2011	Shaun Barron
02	3533	add strength to enclosure	30/05/2012	Shaun Barron



SPECIFICATIONS

VOLTAGE 500Vac
 FREQUENCY 50/60Hz
 CURRENT 25A @ 40°C
 TEMPERATURE -25 TO 100°C
 LEAKAGE CURRENT 67mA @ 500V 50Hz
 HUMIDITY 90% RH (NON-CONDENSING)
 VIBRATION 10-200Hz 1.8G
 ELECTRIC STRENGTH 2250Vac/1min.
 POWER DISSIPATION 11W
 MASS 1.2kg
 TERMINALS 10sqmm TERMINAL BLOCK
 EARTH TERMINALS M5 STUD
 FLANGE MOUNTING 4x M5

RoHS
2002/95/EC
Compliant

Tel No. +44(0)1724 273200 Website www.dem-uk.com

Alpha3 manufacturing
 ROXBURGH EMC
 DELTRON Components
 DELTRON Enclosures
 b.e.s Media

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ALPHA 3 MANUFACTURING.
 ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ALPHA 3 MANUFACTURING IS PROHIBITED.
 DEM Manufacturing, Deltron Emcon House
 Hargreaves Way, Sawcliffe Ind. Park,
 Scunthorpe, North Lincolnshire, DN15 8RF, UK

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MILLIMETRES
 LINEAR TOLERANCE:
 NO DECIMAL PLACES ±0.5mm
 1 DECIMAL PLACE ±0.25mm
 2 DECIMAL PLACES ±0.125mm
 ANGULAR TOLERANCE: ±1°

FINISH	STANDARD FILTER	DEBURR AND BREAK SHARP EDGES
MATERIAL	1.2mm 5052 ALU H14	

DRAWN BY	S BARRON
APPROVED BY	SW
THIRD ANGLE PROJECTION	
SHEET	1 OF 1
SCALE	1:2
PAPER	A4

TITLE	GENERAL SPECIFICATION 3 PHASE 25A 500V INDUSTRIAL FILTER
DRAWING NO.	KMF325A
ISSUE	02
Release	