


**Specification:**

| Model                 | DC.CAB.6400.0150      |
|-----------------------|-----------------------|
| DC Socket             | 5.5/2.5 mm            |
| Recommended voltage   | 0 - 48V               |
| Max Current           | 3 A                   |
| Dielectric Strength   | 500 VDC               |
| Operating temperature | -25°C to +70°C        |
| Cord Length           | 1500 mm               |
| Cable Diameter        | 1,62 x 3,42 mm        |
| Wire Diameter         | 2x0,35mm <sup>2</sup> |
| ROHS                  | +                     |

**Made in Poland**