

779.SILR Cordless LED slim inspection lamp



Description :

- Super slim design to access and illuminate confined spaces.
 - Exceptional Durability: Resistant to impact, water, oil and other workshop lubricants and solvents.
 - Unique semi-rigid soft-contact hook helps prevent damage to contact surfaces and enables hands-free illumination.
 - Two output modes for flexibility in use:
 - Normal : for close up work in confined spaces.
 - Boost : for inspection and general work space illumination.
 - Li-ion rechargeable battery for longer battery life-time.
 - High performance white SMD LEDs with 120° beam.
 - Light output:
 - Normal : 175 lux @ 0.5m (120 lumen)
 - Boost : 350 lux @ 0.5m (240 lumen)
 - Burn time:
 - Normal : 8 Hours.
 - Boost : 4 Hours.
 - Charge and operate simultaneously.
 - Integrated 1/4" thread mounting point for wider hands-free working possibilities.
 - Tether point for additional safety and working at height
 - Delivered with 110 - 240 V AC adaptor, Automotive 12V Cigar socket adaptor and USB lead.
 - Charging time: with AC adaptor 3h. (lamp turned off).
 - Lamp dimensions (max LxWxD): 327 x 45 x 25 mm.
 - Lamp dimensions (head WxD): 28 x 11.5 mm.
- Weight: 160 g. (inc battery)