

# KERN FCE30K10N

Einsteiger-Tischwaage à mobil, handlich, leicht



## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand: KERN

Category: Balances

Product Group: Bench scale

## Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 335 x 400 x 187 mm

Gross weight: 2,840 kg

Net weight: 2,250 kg

Shipping method: Parcel service

## Construction

Casing material: Plastic

Dimensions housing (WxDxH): 270 x 345 x 106 mm

Dimensions of weighing plate (WxDxH): 252 x 228 x 12,5 mm

Material weighing plate: Plastic

Weighing surface (WxD): 252 x 228 mm

## Measuring system

Adjustment options: External calibration

Linearity: 30 g

Readout [d]: 10 g

Recommended adjusting weight: 30 kg (M2)

Reproducibility: 10 g

Resolution: 3000

Stabilisation time: 3 s

Warm up time: 10 min

Weighing range [Max]: 30 kg

Weighing system: Strain gauge

Weighing units: kg

## Display

Display digit height: 2,500 cm

## Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

## Power supply

Charging time: 10 h

Input voltage: 220 V - 240 V AC 50 Hz

n/a: CH EURO UK US

n/a: Mains adapter external

## Power supply

Operating time: 12 h

Operating time (Backlight off): 20 h

Rechargeable battery: Rchrg. battery optional