

TDG S22000K

- Part # : TDG S22000
- Description : Straight grinder
- Clamps : D 3 - 6 mm
- Power : 0,5 cv / 370 W
- Air consumption : 113 l/min. (unloaded)
- Rotation speed : 22000 rpm
- Inlet thread : 1/4" BSPF
- Hose ID : 10 mm (3/8")
- Working pressure : 6,3 bar
- Sound level : 84 dBa
- Vibrations : 1,25 m/s²
- Length : 170 mm
- Weight : 0,7 kg
- Material : Composite body
- Speed : Adjusted by screw
- Triger : Progressive / Safety
- Included : 2 clamps (3 – 6 mm)
- Included : 5 grinding wheels D 3 mm and 5x D 5 mm
- Included : 2 wrenches



Applications

