

STANLEY®
FATMAX®

STANLEY FATMAX 100M Laser Distance Measurer with Bluetooth connectivity (TLM330s) STH1-77140



Features:

- 100m working range
- Accuracy of +/- 1.5mm @10m
- Provides distance, area and volume calculations
- Indirect height measurements via Pythagoras calculation
- Measurement taken from the front, back, tripod mount or end toe of the product
- Toe piece allows measurement from the corner of the room
- Bluetooth connectivity to sync to most smartphones and tablets
- Quickly capture measurements, make photo mark-ups and create custom floor plans by connecting to the STANLEY® Smart Connect™ App
- Addition / subtraction calculator
- Automatic sleep mode
- Colour touch screen
- Memory function
- Rated to IP54 to protect against dust and water spray
- 1/4" Tread for tripod mounting
- Runs on 3x AAA batteries (supplied)

Description:

The STANLEY FATMAX Laser Distance Measurer TLM330s has a working range of 100m with an accuracy of +/- 1.5mm @ 10m and provides distance, area and volume calculations along with a Pythagoras function. With bluetooth connectivity allowing syncing to most smartphones and tablets, the TLM330s quickly captures measurements and creates custom floor plans by connecting to the STANLEY® Smart Connect™ App. The TLM is rated to IP54 to protect against dust and water spray. Compact and lightweight, the TLM330s has a point and click measurement function and runs with 3 x AAA batteries. Easily capture measurements, especially those that would be difficult to capture with a tape measure. Equipped with a multitude of convenient features that make any tradesman's life on the job easier, the TLM330s is ideal for electricians, contractors, masons, remodelers, painters, architects, inspectors, and builders.

Specifications

Product Info	
SKU	STHT1-77140
Type	TLM
Beam Colour	Red
Measuring Range	0.15-100M
Measure Accuracy	+/- 0.15mm/m
Distance	Yes
Continuous Measurement	Yes
Area & Volume	Yes
Add & Subtract	Yes
Pythagoras	1,2,3
Bluetooth	Yes
Touch Screen	Yes
IP Rating	IP54
Thread	¼"
Measuring Points	4 (Front, Back, Tripod and Toe)
Memory	20
Batteries (Supplied)	3 x AAA batteries
Kit Contents	TLM330s & Pouch