




Feature -  
thru-hole terminal  
SPST, SPDT, momentary function

Application -  
instrumentation  
telecommunications and networking equipments  
computer and peripherals  
office and home electrical appliances

► SPECIFICATIONS

SWITCH SPECIFICATIONS	
POLE - POSITION	Momentary action , 1P1T or 1P2T
CONTACT RATING	1Amp with resistive load @ 125VAC or 28VDC
CONTACT RESISTANCE	20 mΩ MAX. 1.5 V DC ; 100 mA , by Method of Voltage DROP
INSULATION RESISTANCE	1000 MΩ MIN. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable ; 1500 V AC for 1 Minute
OPERATING FORCE	250 ± 100 gf
OPERATING LIFE	30,000 cycles
OPERATING TEMPERATURE RANGE	-30°C ~ 85°C
TOTAL TRAVEL	SPST : 1.5 ± 0.3 mm , SPDT : 1.2±0.3mm

► HOW TO ORDER



▶ DIMENSION		
PS008-N11AA		
PS008-N12AB		
▶ CIRCUIT	▶ P.C.B LAYOUT	▶ MATERIAL
1P1T : 	1P1T : 	<ul style="list-style-type: none"> <li>■ FRAME : PA + GF</li> <li>■ ACTUATOR : PA + GF</li> <li>■ BASE FRAME : PA + GF</li> <li>■ TERMINAL : BRASS SILVER PLATING</li> <li>■ MOVING CONTACT : PHOSPHOR BRONZE SILVER PLATING</li> <li>■ SPRING : STAINLESS STEEL</li> </ul>
1P2T : 	1P2T : 	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[PS008-N11AA](#)