

Within Series Adaptor 32_N-75-0-1/133_N

Description

Adaptor plug/plug
N plug (male) / N plug (male)

Interface standard
Series N - Not compatible to N 50 Ohms



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 1.5 GHz

Mechanical Data

Number of matings 500
Weight 0.0533 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - N plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - N plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing DCA-00013682

Ordering Information

Single package 32_N-75-0-1/133_NE

Within Series Adaptor 32_N-75-0-1/133_N