

CAB PC 604022 T3B

FIBOX
Enclosing innovations



Sample image

Order symbol : CAB PC 604022 T3B

Product nr : 8113072

UL Code : 8143072

UL Name : UL CAB PC 604022 T3B

Description : Cabinet, PC, Smoked transparent door


Remarks : Locks on the long side

EAN : 6418074020475

El. number :

- Finland : 3424178
- Denmark : 8212019292
- Sweden : 2539959

Including : Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.



Dimensions :

	Height	Width	Depth
mm :	600	400	220
inch :	23.62	15.75	8.66

Materials :

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	Clear transparent
Gasket material :	Polyurethane

Temperatures :

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

Rating :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

Certificates :

Certificate FI 40854