

CAB PCQ 403017 G



Sample image

Order symbol : CAB PCQ 403017 G

Product nr : 8113358

UL Code : 8143358

UL Name : UL CAB PCQ 403017 G

Description : Cabinet, PC


Remarks : Grey cover

EAN : 6418074011169

El. number :

- Finland : 3421974
- Denmark :
- Sweden : 2539122

Including : Base with screws for mounting plate/DIN-rail. internal corner plugs. cover with PUR gasket and CS 12137 cover screws.



Dimensions :	Height	Width	Depth
mm :	400	300	170
inch :	15.75	11.81	6.69

Materials :

Accessories :

- DRF 43/44 DIN rail frame set, for enclosures:
- PAT 12040 Hinge set
- MB 12225 Swing door set
- AL
- EKIV 37 DIN-35 Mounting rail, for enclosures:

Material : Polycarbonate
Base colour : RAL 7035 -light grey
Cover colour : RAL 7035 -light grey
Gasket material : Polyurethane

Temperatures :

Temperature °C (short term) : -40 ... 120
Temperature °C (continuous) : -40 ... 80
Temperature °F (short term) : -40 ... 250
Temperature °F (continuous) : -40 ... 175

(366 x 35 x 1)
EKIV 27 DIN-35 Mounting rail, for enclosures:
(266 x 35 x 1)
EKIV 43 Mounting plate, for enclosures:
(370 x 270 x 1)
FP A 43 Swing-out door/Front plate (aluminium), for
enclosures:
(268 x 368 x 1)

Rating :

Ingress protection (EN 60529): IP66; IP67;
Impact Resistance (EN 62262): IK08;
Electrical insulation : Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance : UL 508
Flammability Rating : UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C : 960 °C
NEMA Class

Certificates :

Certificate FI 40848