

CAB PC 303018 T



Sample image

Order symbol : CAB PC 303018 T

Product nr : 8113040

UL Code : 8143040

UL Name : UL CAB PC 303018 T

Description : Cabinet, PC, Smoked transparent door


Remarks : Latches on the long side

EAN : 6418074020130

EI. number :

- Finland : 3424157
- Denmark : 8212020236
- Sweden : 2539941

Including : Cabinet base. door with PUR gasket. latches. screws for mounting plate/ DIN-rail and corner plugs.



Dimensions : **Height** **Width** **Depth**

Accessories :

mm :	300	300	180
inch :	11.81	11.81	7.09

Materials :

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	Clear transparent
Gasket material :	Polyurethane

Temperatures :

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

EKIV 33 Mounting plate, for enclosures:
(270 x 270 x 1)

MB 12225
AL Swing door set

FP A 33 Swing-out door/Front plate (aluminium), for
enclosures:
(268 x 268 x 1)

EKIV 27 DIN-35 Mounting rail, for enclosures:
(266 x 35 x 1)

DRF 33 DIN rail frame set, for enclosures:

Rating :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

Certificates :

Certificate FI 40854