

TPC 131308



Sample image

Order symbol : TPC 131308

EAN : 6418074049773

Including :



Product nr : 5824041

El. number :



Description : Enclosure, PC

- Finland :
- Denmark :
- Sweden :

Remarks : Grey cover



TPCM/TAM



Dimensions :	Height	Width	Depth
mm :	130	130	75
inch :	5.12	5.12	2.95

Accessories :

MIV 10	DIN-35 Mounting rail, for enclosures: (100 x 35 x 1)
FP 10674	Wall fastening lug (2 pcs) incl. screws

Materials :

Material :	Polycarbonate
Base colour :	
Cover colour :	
Gasket material :	

Rating :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07; IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	-
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

Temperatures :

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	

Temperature °F (short term) : -40 ... 250

Temperature °F (continuous) : -40 ... 175

Certificates :

Certificate FI 40343