

PC 17/16-C3



Sample image

Order symbol : PC 17/16-C3

EAN : 6418074010179

Including :




Product nr : 7520080

El. number :

Description : Enclosure, PC

- Finland : 3422926
- Denmark : 8212016606
- Sweden :

Remarks : Without main cover



Dimensions :

	Height	Width	Depth
mm :	166	160	108
inch :	6.54	6.3	4.25

Accessories :

FP 17/16	Front plate (aluminium), for enclosures: (160 x 100 x 0)
MP 17/16	Mounting plate, for enclosures: (136 x 133 x 1)
FC PC 17/16	Frame of PC front plate, for enclosures:

Materials :

Material : Polycarbonate

Base colour :

Cover colour :

Gasket material : Polyurethane

(166 x 106 x 16)

Temperatures :

Temperature °C (short term) : -40 ... 120

Temperature °C (continuous) : -40 ... 80

Temperature °F (short term) : -40 ... 250

Temperature °F (continuous) : -40 ... 175

Rating :

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK07;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

Certificates :

SGSFIMKO_CARDpc