

TPC 292411



Sample image

Order symbol : TPC 292411

Product nr : 5824003

Description : Enclosure, PC



Remarks : Grey cover

EAN : 6418074078797

Including :

El. number :

- Finland :
- Denmark :
- Sweden :



2xM20 knock out

Dimensions :

Height

Width

Depth

Accessories :

mm :	289	239	107
inch :	11.38	9.41	4.21

Materials :

Material : Polycarbonate
 Base colour :
 Cover colour :
 Gasket material :

Temperatures :

Temperature °C (short term) : -40 ... 120
 Temperature °C (continuous) :
 Temperature °F (short term) : -40 ... 250
 Temperature °F (continuous) : -40 ... 175

MP 2924	Mounting plate, for enclosures: (265 x 215 x 0)
DR 215	DIN-35 Mounting rail, for enclosures: (215 x 35 x 1)
DR 265	DIN-35 Mounting rail, for enclosures: (265 x 35 x 1)
FP 10674	Wall fastening lug (2 pcs) incl. screws

Rating :

Ingress protection (EN 60529): IP65;
 Impact Resistance (EN 62262): IK07; IK08;
 Electrical insulation : Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance : -
 Flammability Rating : UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C : 960 °C
 NEMA Class

Certificates :

Certificate FI 40343