

# CAB PCQ 404017 G



Sample image

**Order symbol :** CAB PCQ 404017 G

**EAN :** 6418074011183

**Product nr :** 8113488

**El. number :**

UL Code : 8143488


- Finland : 3421982
- Denmark :
- Sweden : 2540101

UL Name : UL CAB PCQ 404017 G

**Description :** Cabinet, PC

**Remarks :** Grey cover

**Including :** Base with screws for mounting plate/DIN-rail. internal corner plugs. cover with PUR gasket and CS 12137 cover screws.



**Dimensions :**

mm :	Height	Width	Depth
400	400	400	170

**Accessories :**

DRF 43/44 DIN rail frame set, for enclosures:

inch : 15.75 15.75 6.69

**Materials :**

Material : Polycarbonate  
Base colour : RAL 7035 -light grey  
Cover colour : RAL 7035 -light grey  
Gasket material : Polyurethane

**Temperatures :**

Temperature °C (short term) : -40 ... 120  
Temperature °C (continuous) : -40 ... 80  
Temperature °F (short term) : -40 ... 250  
Temperature °F (continuous) : -40 ... 175

PAT 12040 Hinge set  
MB 12225 Swing door set  
AL  
EKIV 37 DIN-35 Mounting rail, for enclosures:  
(366 x 35 x 1)  
FP A 44 Swing-out door/Front plate (aluminium), for  
enclosures:  
(368 x 368 x 1)  
EKIV 44 Mounting plate, for enclosures:  
(370 x 370 x 1)

**Rating :**

Ingress protection (EN 60529): IP66; IP67;  
Impact Resistance (EN 62262): IK08;  
Electrical insulation : Totally insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
UV resistance : UL 508  
Flammability Rating : UL 746C 5"  
Glow Wire Test (IEC 695-2-1) °C : 960 °C  
NEMA Class

**Certificates :**

Certificate FI 40848