

# CAB PC 604022 G3B



Sample image

**Order symbol :** CAB PC 604022 G3B

**Product nr :** 8113372

UL Code : 8143372

UL Name : UL CAB PC 604022 G3B

**Description :** Cabinet, PC, Grey door


**Remarks :** Locks on the long side

**Including :** Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

**EAN :** 6418074020468

**El. number :**

- Finland : 3424128
- Denmark : 8212019289
- Sweden : 2539985



**Dimensions :**

	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	600	400	220
inch :	23.62	15.75	8.66

**Materials :**

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

**Temperatures :**

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

**Rating :**

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

**Certificates :**

Certificate FI 40854