


PC 21/18-C3



Sample image

Order symbol : PC 21/18-C3

EAN : 6418074010216

Including :


Product nr : 7520081

El. number :

Description : Enclosure, PC

- Finland : 3422928
- Denmark : 8212016619
- Sweden :

Remarks : Without main cover



Dimensions :	Height	Width	Depth
mm :	213	185	90
inch :	8.39	7.28	3.54

Materials :

Material :	Polycarbonate
Base colour :	
Cover colour :	
Gasket material :	Polyurethane

Accessories :

FP 21/18	Front plate (aluminium), for enclosures: (207 x 119 x 1)
FC PC 21/18	Frame of PC front plate, for enclosures: (213 x 125 x 20)
MP 21/18	Mounting plate, for enclosures: (142 x 200 x 1)

Rating :

Ingress protection (EN 60529):	IP66; IP67;
--------------------------------	-------------

Temperatures :

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

Impact Resistance (EN 62262):	IK07;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

Certificates :

SGSFIMKO_CARDpc