



VENID Visual harmony

As part of a modern conference room, the desk connection panel VENID offers both exceptional design and high functionality. The original desktop material can be fitted quickly and easily in the mounting frame, so the desktop and connection panel form a harmonious unit.

Perfectly integrated in the surface, VENID not only looks elegant but also offers a practical benefit, as the necessary cables can be conveniently stowed in the desk. The cover, which can be raised in either direction, is easy to operate and leaves room for the cables is easy to operate and leaves enough room for the cables to stay plugged in when closed. Two multiple-socket outlets can be integrated in the VENID tray and equipped individually. The mounting frame and tray are available separately, so existing cable duct systems can continue to be used without a problem

The benefits at a glance

- $\cdot\,$ Harmonious surface thanks to visually smooth integration
- $\cdot\,$ Can be operated from either side for ease of use
- $\cdot\,$ Practical benefit of optional cable storage
- · Flexible equipment options for PDU

www.bachmann.com

VENID

ENID mou	unting frame	Dimensions approx. 351 x 180 mm	
lack anodis	sed aluminium		
935.000	 with mount to clip in the VENID tray 		No.
	Cover can be opened on both sides with end stop		
	• The cut-out part of the original desktop is fitted in th	ne inner frame	
	• Max. desktop thickness up to 25 mm		
ENID trav			
		Dimensions approx. 336 x 163 x 118.5 mm	
ENID tray heet steel, 935.100	(optional)		

4-way: 2 x o	ustom module + power socket outlets	Length: approx.	229 mm	С
Anodised alu	minium profile; power input 0.2m cable and GST18 plug, incl. mounting bracke	t		
936.007	\cdot 2 x socket outlet with earthing contact, shuttered, black, set at 35°			
936.008	\cdot 2 x French / UTE socket outlet, shuttered, black, set at 35°			

4-way: 1 x c	ustom module + power socket outlets	Length: approx. 229 mm	С
Anodised alu	minium profile; power input 0.2 m cable and GST18 plug, incl. mounting bracket		
936.009	\cdot 3 x socket outlet with earthing contact, shuttered, black, set at 35°		
936.010	\cdot 3 x French / UTE socket outlet, shuttered, black, set at 35°		
936.015	\cdot 3 x Swiss / CH T13 socket outlet, shuttered, black, set at 0°		+
936.012	\cdot 2 x Italian / earthing contact combination, shuttered, black, set at 35°		
936.011	\cdot 2 x UK 3.15 A individually fused, shuttered, black, set at 45°		



936.007

4-way: 1 x U	SB double charger (5.2 V / 2.15 A) + 2 x custom module + power socket outlets	L: approx. 229 mm	С
Anodised alu	minium profile; power input 0.2m cable and GST18 plug, incl. mounting bracket		
936.003	· 1 x socket outlet with earthing contact, shuttered, black, set at 35°		
936.004	\cdot 1 x French / UTE socket outlet, shuttered, black, set at 35°		
936.013	· 1 x Swiss / CH T13 socket outlet, shuttered, black, set at 0°		+



4-way: 1 x U	SB double charger (5.2 V / 2.15 A) + 1 x custom module + power socket outlets L: approx. 229 mm	CU
Anodised alu	minium profile; power input 0.2 m cable and GST18 plug, incl. mounting bracket	
936.001	\cdot 2 x socket outlet with earthing contact, shuttered, black, set at 35°	
936.002	\cdot 2 x French / UTE socket outlet, shuttered, black, set at 35°	
936.014	\cdot 2 x Swiss / CH T13 socket outlet, shuttered, black, set at 0°, without custom module	+
936.006	 1 x Italian / earthing contact combination, shuttered, black, set at 35° 	
936.005	 1 x UK 3.15 A individually fused, shuttered, black, set at 45° 	



CUSTOM MODULES

BACHMANN custom modules are the central components of video, audio and network connections, and fit easily and flexibly into BACHMANN power strips with custom module covers.

With the easy-to-swap modules, you can create units to meet the individual data, video and audio connection requirements of your customers quickly and simply.



All custom modules and accessories such as device supply cables are available in our catalogues, on request and on our website at www.bachmann.com.