

# ARCA 406021W



Sample image

**Order symbol :** ARCA 406021W

**Product nr :** 8120146

**Description :** Cabinet, PC


**Remarks :** Grey cover with window, 2-point locking, hinges on the short side

**EAN :** 6418074080172

**El. number :**

- Finland : 3423225
- Denmark : 8212092028
- Sweden : 2500145

**Including :** Cabinet base. door with PUR gasket. mounting plate. screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.



Dimensions :	Height	Width	Depth
mm :	400	600	210
inch :	15.75	23.62	8.58

## Materials :

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	Clear transparent
Gasket material :	Polyurethane

## Accessories :

MPS ARCA 6040	Mounting plate (550x350x2 mm) (550 x 350 x 2)
PMK ARCA 60	PoleMounting kit, for pole $\varnothing$ 100-300mm (585 x 385 x 35)
MPP ARCA 4060	Mounting plate perforated (550x350x2 mm - 26x11 mm) (350 x 550 x 2)
DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
IDS ARCA 4060	Inner door set (385 x 585 x 35)

**Temperatures :**

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
SBK ARCA 40	Support bar kit (340 x 40 x 30)
MPMP ARCA 6040	Mounting plate multiperforated (550x350x2 mm - ø3.6 mm) (550 x 450 x 2)
DRS ARCA 406021	DIN rail frame set (585 x 385 x 35)
MPX ARCA 6040	Mounting plate (550x350 mm) (550 x 350 x 5)
SBK ARCA 60	Support bar kit (535 x 40 x 30)
RCS ARCA 4060	Rain canopy set for size 4060 (20 x 600 x 30)

**Rating :**

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

**Certificates :**

Certificate FI 40467