

# CAB PCQ 604027 G



Sample image

**Order symbol :** CAB PCQ 604027 G

**Product nr :** 8113478

**Description :** Cabinet, PC


**Remarks :** Grey cover

**EAN :** 6418074011206

**El. number :**

- Finland : 3421980
- Denmark :
- Sweden : 2540105

**Including :** Base with screws for mounting plate/DIN-rail. internal corner plugs. cover with PUR gasket and CS 12137 cover screws.



Dimensions :	Height	Width	Depth
mm :	600	400	270
inch :	23.62	15.75	10.63

Accessories :	
EKIV 64H	Mounting plate, for enclosures: (570 x 370 x 1)
PAT 12040	Hinge set

**Materials :**

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

MB 12225 AL	Swing door set
EKIV 37	DIN-35 Mounting rail, for enclosures: (366 x 35 x 1)
DRF 63/64	DIN rail frame set, for enclosures:
FP A 64	Swing-out door/Front plate (aluminium), for enclosures: (568 x 368 x 1)

**Temperatures :**

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

**Rating :**

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

**Certificates :**

Certificate FI 40848